

Pin and Sleeve Strain Relief Adapter.60A,1-inch NPTFitting.



## Features & Benefits

All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.

And all feature chemical-resistant thermoplastic construction.

An exclusive, hinged cord grip eliminates loose parts that get lost.

North American products come completely ready to wire, for quick, simple installation.

Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Commercial	Standard	UL Listed

### Dimensions

Product Width US	2.0 in	Product Height US	2.0 in
Product Length US	2.08 in		

### Technical Information

Amperage	60 A	Wire Size	2 AWG
Voltage	600.0 V		