

CAM TYPE MALE TO MALE COUPLER



Features & Benefits

Quality Materials, durability, and time-tested design

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Application Sector	Commercial/Industrial
Standard	cCSAus		

Technical Information

Amperage	400 A	Wire Size	2/0 - 4/0
Voltage	600.0 V	Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4