

15A GFCI works with the existing three-wire PlugTail connectors creating a non-feed thru application for facility owners. At roughin, just install the same right-angle connector for GFCI and receptacle openings. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

## Features & Benefits

Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock® Protection Faster, more reliable installation feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected

No exposed terminals create a finger-safe application before, during, and after installation

Built-in connector features large brass terminal blades to ensure consistent,  $reliable \ electrical \ connections \ to \ Plug Tail$ Connector

GFCI works with the existing 3-wire PlugTail connectors creating a non-feed-through application for facility

Zinc-plated steel mounting strap

## **Specifications**

General Info					
Product Line	Pass & Seymour	Color	White		
Finish	Matte	Country Of Origin	China		
Number of Receptacles	2	Outlet Type	Commercial, GFCI, Indoor, Self-Test, Tamper- Resistant		
Application Sector	Residential/Commercial	Standard	cULus, UL Listed, FSUL		
Warranty Type	1-Year Limited Warranty	Туре	Outlet		
Dimensions					
Product Width US	1.72 in	Product Depth US	1.2 in		
Product Height US	4.2 in				
Listing Agencies / 3rd Party Agencies					
cULus Listed	Yes				
Technical Information					
Is Tamper-Resistant	Yes	Interrupt Rating	4 A		
Frequency Rating	60 Hz	Trip Range	5±1 mA		

Amperage	15 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	Voltage	125.0 V