




Pass and Seymour

PlugTail® Specification Grade 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Light Almond

Part No. PT2097LA



20A GFCI works with the existing three-wire PlugTail connectors creating a non-feed thru application for facility owners. At rough-in, just install the same right-angle connector for GFCI and receptacle openings. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock® Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected

Faster, more reliable installation

No exposed terminals create a finger-safe application before, during, and after installation

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector

GFCI works with the existing 3-wire PlugTail connectors creating a non-feed-through application for facility

Zinc-plated steel mounting strap

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	Commercial, GFCI, Indoor, Self-Test
Application Sector	Residential/Commercial	Standard	cULus, UL Listed, FSUL
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.72 in	Product Depth US	1.2 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Interrupt Rating	4 A	Frequency Rating	60 Hz
Trip Range	5±1 mA	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Voltage	125.0 V		
