



Pass and Seymour
PlugTail® Specification Grade Three-Way Illuminated 20A Toggle Switch, White
Part No. PT20AC3WSL



3-way Illuminated Toggle Switch, 20A 120/277V For detailed PlugTail information, visit our PlugTail Headquarters.

Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Shallow design for easier installation.

No exposed terminals create a finger-safe application before, during, and after installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Impact- and chemical- resistant cover.

One-piece nickel-plated mounting strap for superior corrosion resistance.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------------------|
| Product Line | Pass & Seymour | Color | White |
| Country Of Origin | Mexico | Application Sector | Residential/Commercial |
| Standard | UL 20 | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|-----------------|-------------|----------------|-------------------|
| Actuator | Toggle | Contact Rating | 20Amp, 120/277Vac |
| Amperage | 20 A | Action | DPDT |
| Number of Poles | Double Pole | Voltage | 120.0 V |
