



Pass and Seymour
PlugTail® Connector in Orange, Right Angle, Solid, 6-in XHHW-2 Wire
Part No. PTR6SOLOR

PlugTail® Connectors, Right Angle, Solid, 6-inch PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle. Orange connector makes identifying isolated ground circuits easier.

Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Distinguished orange connector head to help identify isolated ground circuits during rough in or device replacement.

PlugTail™ Orange Connector: #12 AWG, THHN, copper conductor, 6 - in leads, stripped, solid, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Orange	Country Of Origin	Mexico
Construction	Injection molded plastic	Features	Plug-In, Right Angle
Package Quantity	1	Application Sector	Commercial
Standard	RoHS, cULus	Warranty Type	1-Year

Dimensions

Product Width US	1.0 in	Product Weight US	0.06 lb
Product Height US	1.0 in	Product Length US	6.0 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Wire Size	12 AWG	Indoor/Outdoor	Indoor
-----------	--------	----------------	--------

Connection Type	Wired	Environmental Conditions	0 to 95% (relative humidity, non-condensing)
-----------------	-------	--------------------------	--
