



Pass and Seymour
NAFTA-Compliant PlugTail® Connectors, Right Angle, Stranded, 6-in
Part No. PTR6STRNA



PlugTail® Connectors, Right Angle, Stranded, 6-inch, NAFTA-Compliant PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

NAFTA-Compliant

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Plated steel wrap strap design for maximum durability and corrosion resistance.

Available in any wire length up to 25 inches, use Configurable Solutions to order.

For covering patents, see www.legrand.us/patents.

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, stranded, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	Mexico
Application Sector	Commercial	Standard	cULus UL498, NAFTA-Compliant

Dimensions

Product Length US	6.0 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Temperature Rating	-40° - 60° C
---------------------	--------------------------	--------------------	--------------

Wire Size	12 AWG
-----------	--------
