



radiant Collection
radiant® 15A Tamper-Resistant Ultra-Fast USB Type A/C Outlet, Graphite
Part No. R26USBAC6G



Charge phones, tablets and more up to 40% faster, with Ultra-Fast USB Outlets from the radiant® Collection. With an industry-leading 27W of power supplying the included USB Type-A and USB Type-C connections, this outlet helps you get that full battery feeling with convenience and speed – no bulky adapters needed. Easily replacing traditional outlets in as little as ten minutes, the Ultra-Fast updates your space with advanced functionality and the sleek, clean lines of radiant for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Provides fast and convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.

Includes connections for both traditional USB Type-A and the newer USB Type-C, to accommodate all mobile devices.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Features an industry-leading 6.0A of power, as well as Smart Chip technology, to maximize charging speed for each USB connection.

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

| | | | |
|-------------------|--------------------------------|-------------------------|---|
| Product Line | Pass & Seymour | Replaced by Part Number | |
| Color | Graphite | Finish | Graphite |
| Country Of Origin | China | Number of Receptacles | 2 |
| Features | USB-A Charging, USB-C Charging | Outlet Type | Indoor, Residential, Tamper-Resistant, USB-Charging |
| Warranty Type | 1-Year Limited Warranty | Type | Outlet |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 1.693 in | Product Depth US | 1.35 in |
| Product Height US | 4.18 in | | |

Technical Information

| | | | |
|--------------------------|---|-------------------------|-------------|
| Is Tamper-Resistant | Yes | USB Amperage | 6 A |
| Number of USBs | 2 | USB Power Output | 15 W |
| Amperage | 15 A | Number of Poles | Double Pole |
| Indoor/Outdoor | Indoor | NEMA Configuration Code | 5-15R |
| Mounting Type | Box | Voltage | 125.0 V |
| Environmental Conditions | 95% (relative humidity, non-condensing) | | |
