



radiant Collection
radiant® 120V, 700VA, Magnetic Low-Voltage Single Pole/3-Way Dimmer, Tri-Color
Part No. RHLV703PTC



Upgrade your space with precise dimming control and exceptional style, while saving energy and extending bulb life by reducing the amount of electricity required to power the lights. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Usable in both single-pole and 3-way applications.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Ivory, Light Almond, White	Country Of Origin	China
Switch Type	Paddle	Number of Switches	1
Application Sector	Residential	Standard	CSA Listed, cULus, UL Listed
Warranty Type	Limited Lifetime Warranty	Type	Dimmer

Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
------------------	---------	------------------	---------

Product Height US 4.25 in

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
------------------	--------------	------------	-----------------

Number of Gangs	1	Amperage	15 A
-----------------	---	----------	------

Bulb Compatibility	Halogen	Number of Poles	3-Way, Single Pole
--------------------	---------	-----------------	--------------------

Wattage	700 W	Mounting Type	Box
---------	-------	---------------	-----

Voltage	120.0 V	Load	Low Voltage
---------	---------	------	-------------

Environmental Conditions	Humidity: Less than 95% non condensing		
--------------------------	--	--	--
