



60As Replacement Switch

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Blue
Country Of Origin	Germany	Application Sector	Industrial
Standard	UL, CSA		

### Dimensions

Product Width US	7.3 in	Product Depth US	7.1 in
Product Height US	11.6 in		

### Listing Agencies / 3rd Party Agencies

cUL Listed	Yes
------------	-----

### Technical Information

Contact Configuration	(Optional) 1 N.O. & 1 N.C.	Contact Rating	(Optional) 10A @ 600VAC
Amperage	60 A	Voltage	600.0 V

Environmental Conditions	Moisture Resistance: Per UL50, Section 35, NEMA Enclosure Type 4X (watertight, hosedown), Type 12K (dusttight, falling dirt), and IP67 suitability: Flammability: UL94 5VA and V0 Classification: UV Resistance: All enclosure materials are UV stable
--------------------------	---