

Pass and Seymour Combination Openings, 1 Blank and 1 Duplex Receptacle, Two Gang, White Part No. SP138W

Combination Wall Plate, 1 Blank and 1 Duplex Receptacle, 2-Gang



## Features & Benefits

| Molded of non-combustible mar-proof material.   | Available in 'SP' series in Standard, Junior-Jumbo,<br>and Jumbo sizes. |
|---|---|
| Seven standard colors available Ivory, White, Brown, Gray, Black,<br>Red, and Light Almond. | Individually wrapped with color-matching screws.                        |
| Resistant to discoloration, grease, oil, solvent, and moisture.                             | Nominal thickness, .070 inch.   |

## Specifications

## General Info

| Product Line                          | Pass & Seymour         | Color            | White                      |  |
|---------------------------------------|------------------------|------------------|----------------------------|--|
| Country Of Origin                     | Mexico                 | Wall Plate Type  | Blank, Combination, Outlet |  |
| Application Sector                    | Residential/Commercial | Standard         | CSA, UL514                 |  |
| Dimensions                            |                        |                  |                            |  |
| Product Width US                      | 4.56 in                | Product Depth US | 0.2 in                     |  |
| Product Height US                     | 4.5 in                 |                  |                            |  |
| Listing Agencies / 3rd Party Agencies |                        |                  |                            |  |
| CSA Listed                            | Yes                    | CSA File Number  | 17695                      |  |
|                                       |                        |                  |                            |  |

## Technical Information

| Cutout          | Blank and Receptacle | Thickness     | 0.07 in        |
|-----------------|----------------------|---------------|----------------|
| Number of Gangs | 2                    | Mounting Type | Exposed Screws |