



radiant Collection
radiant® 20A Tamper Resistant Ultra Fast PLUS Power Delivery USB Type C/C Outlet, Red
Part No. TR20USBPRED



20A Tamper-Resistant Ultra Fast PLUS Power Delivery USB Type CC Outlet Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Charge the latest devices up to 2X as fast, thanks to the industry-leading 6.0A of our Ultra-Fast line and a whopping 30W of power courtesy of advanced Power Delivery

Provides fast and convenient built-in charging through two future-proof USB Type-C ports, accommodating new and upcoming devices without an adapter

Includes multiple layers of overcurrent protection, ensuring the outlet and your favorite devices can charge at optimal levels without risk of damage

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect

More color options available to fit any style, including finishes to match current hardware and lighting trends

Built for intelligent charging, the outlet detects and delivers the precise amount of power needed to maximize charging speeds

Helpful indicator light lets you see charging status at a glance. Light glows yellow while charging is in progress, and shows green once the device battery is sufficiently charged

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty

Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Red	Finish	Matte
Country Of Origin	China	Features	USB-C Charging
Outlet Type	USB-Charging	Application Sector	Commercial
Type	Tamper-Resistant, USB		

Dimensions

Product Width US	1.69 in	Product Depth US	1.42 in
------------------	---------	------------------	---------

Product Height US	2.63 in
-------------------	---------

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

USB Amperage	6 A	Connection	USB Type C/C
--------------	-----	------------	--------------

Number of USBs	2	USB Power Output	30 W
----------------	---	------------------	------

Amperage	20 A	Current Rating	20 A
----------	------	----------------	------

Indoor/Outdoor	Indoor	Mounting Type	Box
----------------	--------	---------------	-----

Voltage	125.0 V
---------	---------
