



Pass and Seymour
15A 125V Fed Spec-Grade Tamper-Resistant USB Type A/A Outlet, Black
Part No. TR5262USBBK



Designed for commercial markets with strength and durability in mind, this combination duplex receptacle and two USB Type-A features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.

Auto-ground clip assures positive ground.

AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects.

Multiple color options available.

Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire.

Stainless steel auto-ground clips assure positive ground.

Wire Size: #14 - #10 AWG Copper Conductor Only

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	Country Of Origin	Vietnam
Number of Receptacles	2	Features	USB-A Charging
Outlet Type	Commercial, Indoor, Tamper-Resistant, USB-Charging	Application Sector	Commercial
Standard	CSA Listed, cULus, FSUL, UL Listed, RoHS	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.693 in	Product Depth US	1.392 in
------------------	----------	------------------	----------

Product Height US	2.677 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
---------------------	--------------------------	---------------------	-----

USB Amperage	3.1 A	Number of USBs	2
--------------	-------	----------------	---

USB Power Output	15 W	Temperature Rating	-40° - 60° C
------------------	------	--------------------	--------------

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
-----------	-------------	----------------	--------

Voltage	125.0 V
---------	---------
