



Pass and Seymour  
20A 125V Hospital-Grade Tamper-Resistant USB Type A/A Outlet, White  
Part No. TR8300HUSBW



Designed for the healthcare market and capable of withstanding heavy use due to its UL Hospital Grade certification. Features include an improved overall 3.1A USB charging capability, auto-ground clips, zinc-plated ground terminal screw, as well as triple-wipe brass contacts for lasting retention. The screw-pressure-plate back wiring makes installation fast and easy. Also available in black, green, gray, ivory, light almond, nickel, red and white. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices

Multiple color options available.

Stainless steel auto-ground clips assure positive ground.

AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects.

Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	Vietnam
Number of Receptacles	2	Features	USB-A Charging
Outlet Type	Commercial, Indoor, Tamper-Resistant, USB-Charging	Type	Outlet

### Dimensions

Product Width US	1.693 in	Product Depth US	1.392 in
Product Height US	2.677 in		

## Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

### Technical Information

---

Is Tamper-Resistant	Yes	USB Amperage	3.1 A
Number of USBs	2	USB Power Output	15 W
Amperage	20 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	Voltage	125.0 V

---