

High-performance splitter designed for digital cable, On Demand, Pay-per-View and high-speed cable Internet.



## Features & Benefits

Strong 15 dB RF video amplification improves signal throughout the home system

Bracket included.

DC passing between all ports.

Uses standard F type connectors.

Handles up to eight outputs and one input.

1 GHz Bandwidth.

## Specifications

### General Info

Product Line	On-Q	UPC Number	804428021629
Country Of Origin	China		

### Additional Information

RoHS Conformant	Yes
-----------------	-----

### Technical Information

Temperature Rating	-40° - 140° F	Insertion Loss	11.1 dB
--------------------	---------------	----------------	---------