# 

Pass and Seymour 250V Weather-Resistant Tamper-Resistant Heavy Duty Spec Grade 20A Single Receptacle with Back and Side Wire Connections, Gray Part No. WR5871TRGRY

Weather-Resistant Tamper-Resistant Heavy Duty Spec Grade Single Receptacle, Back and Side Wire, 20A, 250V



## Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly	One-piece brass, triple-wipe power contacts for lasting retention
Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring	Impact-resistant nylon face and thermoplastic back body
Internal screw-pressure-plate back wire capable of accepting 14 to 10 AWG solid or stranded copper or copper-clad wire	Terminal compartments isolated from each other for positive conductor containment
Tri-drive terminal and mounting screws	Auto-ground clip assures positive ground
WR marking on face as required by UL Standard	

# Specifications

# General Info Product Line Pass & Seymour Color Gray Finish Glossy Country Of Origin Mexico Recentacle Type Single Number of Recentacles 1

Receptacle Type	Single	Number of Receptacles	I
Outlet Type	Weather-Resistant	Application Sector	Commercial
Standard	UL, CSA	Warranty Type	1-Year Limited Warranty
Type Outlet, Tamper-Resistant, Weather-Resistant			

## Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	E140596
cULus Listed	Yes	CSA File Number	C22.2 No. 42

### Technical Information

ls Tamper-Resistant	Yes	Connection	Back and/or Side Wire
Amperage	20 A	Wire Size	14 - 10 AWG
ls Weather Resistant	Yes	Indoor/Outdoor	Outdoor
Mounting Type	Box	Voltage	250.0 V
Connection Type	Wired	Environmental Conditions	Flammability: UL94 V2