



The TracJack, recessed 75 ohm, F-Type, female to female connector, Fog White Adapter Plate, has a single Recessed F-Type, 75Ω, feedthrough connector, mounted at a 180° exit angle. F-connectors are often used with RG-6 and RG-59 75 ohm coaxial cable to connect equipment supporting cable TV(CATV), satellite TV, close circuit TV(CCTV), and security cameras. This adapter panel is 1 unit high. TracJack modules offer flexibility with structured cabling at the workstation or in furniture with a modular design and a wide variety of connectivity options. Intelligent engineering simplifies and speeds up moves, adds, and changes with a front removeable design. Compatible With: All TracJack faceplates

Features & Benefits

Meets Category 5e standard: Ensures standards compliance.

Low profile connector: Allows furniture to be placed closer to the wall.

Designed for multiple coax cable styles: Accepts both push-style and screw-style.

75 Ohm F-connector: Ideal for cable/satellite TV, cable modems, and security cameras.

Standard TracJack footprint: Fits in all TracJack faceplates and housings.

Front removable module: Less intrusive access for adds, moves, changes.

Integrates with Legrand | Wiremold : Can be used in raceway, floor boxes, Poke-Thru, and work surface portals

Specifications

General Info

| | | | |
|-------------------|---------------------------|--------------------|--------------|
| Product Line | Ortronics | UPC Number | 662875834779 |
| Country Of Origin | Taiwan, Province Of China | Application Sector | Commercial |
| Standard | UL Standard | Type | Workstation |

Dimensions

| | | | |
|-------------------|---------|------------------|----------|
| Product Width US | 0.73 in | Product Depth US | 0.875 in |
| Product Height US | 0.92 in | | |