



Pass and Seymour
Stainless Steel Cord Grip, 1 1/4-in Straight, 1.0-1.12 OD Range
Part No. CGSS1251125



The Pass and Seymour series of corrosion-resistant cord connectors feature a body and compression nut made of Type 304 stainless steel with exceptional tensile strength and the highest levels of durability in severely corrosive environments. All stainless steel cord grips include an embedded Buna-N O-Ring. These connectors are recommended for use in washdowns or high moisture environments in food processing plants, petrochemical facilities, wastewater treatment plants, pulp and paper mills and chemical manufacturing factories. (Note: Type 316 stainless steel also available upon request and minimums may apply.)

Features & Benefits

304 grade Stainless Steel construction provides exceptional tensile strength and resists corrosion and impacts

Includes an embedded Buna-N O-Ring providing a long term seal and protection against ingress

The combination tightening surface provides a large wrenching area for easy installation

Available in straight male from 3/8: to 3: NPT

Also available in 316 grade stainless steel, upon request. Minimums may apply

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Construction	Stainless Steel Cord Grip	Application Sector	Commercial/Industrial
Standard	UL Listed, CSA Listed		

Technical Information

Maximum Cable Range	0.87 in	Minimum Cable Range	1 in
---------------------	---------	---------------------	------