



Pass and Seymour
Portable 15A Right Angle Self-Test GFCI Plug, Automatic Reset
Part No. 1597CMA



Plug this Right Angle Portable GFCI (Automatic Reset) into a standard outlet to provide GFCI protection when attached by the user to corded portable equipment such as drills, saws, pressure washers, power painters, etc. outdoors, on construction sites, or anywhere a GFCI-protected receptacle might not be accessible. Ground-Fault Circuit Interrupters (GFCI) help prevent electrical shock caused by ground faults.

GFCI protection is required by code in bathrooms, kitchens, garages, outdoor areas, and for any other outlets found within six feet of a sink or water source.

Features & Benefits

Protects against electrical shock caused by ground-fault occurrences.

Conducts an industry-leading automatic self-test every 3 seconds. If the portable GFCI device ever fails, the red indicator light flashes to signal it should be replaced.

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected. Open neutral relay automatically cuts power to device line conductor if the neutral wire preceding the portable GFCI becomes damaged.

Automatically energizes portable GFCI for use upon plug-in and after loss of primary power.

Specifications

General Info

| | | | |
|--------------|-----------------|--------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Black |
| Finish | Matte | Country Of Origin | China |
| Outlet Type | GFCI | Application Sector | Residential/Commercial |
| Standard | RoHS, UL, cULus | Warranty Type | 1-Year Limited Warranty |
| Type | Straight Blade | | |

Dimensions

| | | | |
|------------------|---------|-------------------|--------|
| Product Width US | 2.0 in | Product Weight US | 0.5 lb |
| Product Depth US | 1.75 in | Product Height US | 4.0 in |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|-----|--------------|-----|
| cULus ListingNumber | 943 | cULus Listed | Yes |
|---------------------|-----|--------------|-----|

Additional Information

| | |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

Technical Information

| | | | |
|---------------------|----|----------|------|
| Is Tamper-Resistant | No | Amperage | 15 A |
|---------------------|----|----------|------|

| | | | |
|----------------------|----|----------------|---------|
| Is Weather Resistant | No | Indoor/Outdoor | Outdoor |
|----------------------|----|----------------|---------|

| | | | |
|-------------------------|-------|---------|---------|
| NEMA Configuration Code | 5-15P | Voltage | 125.0 V |
|-------------------------|-------|---------|---------|
