



Pass and Seymour
WaterTight Straight Blade IP67 Connector 15A 250V 6-15R, Yellow
Part No. 15W49



Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour plugs and connectors feature multiple seals to ensure protection against the environment. Constructed of a sturdy rubber body, which makes them impact- and chemical-resistant, they have nickel-plated blades and contacts for superior corrosion resistance.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

Multi-point sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color-coded sealing bushings provided for large range of cord diameters

For covering patents, see www.legrand.us/patents.

Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.

Devices resist high-pressure hose down of 1,500 psi.

Large ribs on body for a superior grip when mating.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Application Sector	Residential/Commercial
Standard	UL498		

Dimensions

Product Width US	1.85 in	Product Length US	2.62 in
------------------	---------	-------------------	---------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	NO
------------	-----	-----------------	----

Technical Information

Phase	3	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	18 - 12 AWG	Voltage	125.0 V
