



Spec-Grade Isolated Ground Tamper-Resistant 20A Self-Test Duplex GFCI

Features & Benefits

Spec-Grade GFCI self-test One-piece, brass, triple-wipe power contacts for lasting retention.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Number of Receptacles	2
Outlet Type	Commercial, GFCI, Indoor, Self-Test, Tamper-Resistant	Application Sector	Residential/Commercial
Standard	cULus, UL Listed, FSUL	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Is Tamper-Resistant	Yes	Interrupt Rating	4 A
---------------------	-----	------------------	-----

Frequency Rating	60 Hz	Trip Range	5±1 mA
Connection	Back and Side Wire	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Voltage	125.0 V	Environmental Conditions	95% Humidity, UL 94 V2