



Double Three-way Combination Switch, 15 amps, 120/277 volts, Ivory.



## Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	693IG
Color	Ivory	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL20
Type	Combination		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

Contact Configuration	N-O	Operating Cycles	30000
-----------------------	-----	------------------	-------

Actuator	Toggle	Connection	Side wire, non-grounding
Contact Rating	15 Amp, 120/277 VAC	Amperage	15 A
Action	(2) 3W	Number of Poles	3-Way
Voltage	0.433 V	Environmental Conditions	Flammability: UL94 V2