



Pass and Seymour
Discontinued - Titan Series LED 4-Wire Single-Pole Dimmer, Ivory
Part No. CD4FBLI



P&S Titan Dimmers offer a complete solution for easy, economical multi-gang dimmer installation in commercial jobs. Designed to handle 0-10V dimming in Fluorescent and LED fixtures.

Features & Benefits

Includes integrated power pack and blank center plate.

Labeling system.

Shipped with protective film.

Superior ratings with a minimum of derating when ganged.

For covering patents, see www.legrand.us/patents.

Field configurable wall plate system.

Adjustable low end trim.

Rugged construction.

Simple to plan the rough-in.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	China	Application Sector	Commercial
Standard	RoHS, cULus	Type	Dimmer

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Amperage	10 A	Number of Poles	Single Pole
Voltage	120.0 V	Load	Fluorescent
Environmental Conditions	Humidity: Less than 95% non condensing		