



Pass and Seymour
TurnLok® 50A Corrosion-Resistant 125/250V 3-Pole 4-Wire Locking Connector
Part No. CR6364C



50A Turnlok Plugs and Connectors make installing and securing your connections faster, safer and more dependable than ever. These devices are designed to withstand harsh environments. Each device features a simple push, twist and lock body assembly for greater productivity and labor savings in temporary power applications. The back body easily slides onto the device and locks in place with a quarter twist making installations faster, safer and more dependable.

Features & Benefits

Securing your installations is easier than ever. The back body easily slides onto the device and locks in place with a simple quarter twist. No time-consuming threading.

Same-plane hex head terminations for faster, easier and safer terminations that allow more torque to be applied without the risk of harmful screwdriver slips. All termination screws are on the same plane for a more accurate and streamlined installation that saves you precious time on the job.

Impact- and corrosion-resistant durable nylon 66 shell material.

Newly designed external cord grips provide visible assurance of safe and proper cord retention.

An adjustable cord clamp is located outside the back body for greater flexibility to accommodate a wider range of cord sizes. Clamp screws are on the same plane for faster installation. Longer screws are included to adjust for larger cables.

Industrial-strength, brass alloy plug blades and connector contacts resist heat rise and provide excellent conductivity.

Visible molded NEMA configuration and device rating.

Integral flexible rubber cord gromet conforms to and seals around SO cord to provide protection from oils, water or chips entering wiring chamber.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007442595	Country Of Origin	Mexico
Application Sector	Commercial/Industrial	Standard	RoHS, UL UL498, cULus E146159
Type	Locking Connector		

Dimensions

Product Width US	2.86 in	Product Height US	2.86 in
------------------	---------	-------------------	---------

Product Length US	6.16 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Number of Wires	4	Contact Material	Brass
-----------------	---	------------------	-------

Amperage	50 A	Voltage	250.0 V
----------	------	---------	---------
