



Pass and Seymour  
**20A NEMA Connector L520 - Yellow Back, White Front Body, Corrosion-Resistant**  
Part No. CRL520C

Turnlok® Connector 3-Wire 20A 125V Corrosion Resistant



## Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.	Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity. Raised ribs provide non-slip gripping profile for turning to lock and unlock.
Double dovetail design provides superior protection against cord pull-out forces.	Impact- and corrosion-resistant durable nylon 6 shell material.
Rounded back contour reduces snags and hang-ups on the job site.	Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
Visible stamped NEMA configuration and device rating.	New-design external cord grips provide visible assurance of safe and proper cord retention.
Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.	

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Application Sector	Industrial
Standard	UL Listed		

### Dimensions

Product Width US	2.2 in	Product Length US	3.33 in
------------------	--------	-------------------	---------

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

Phase	3	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Voltage	125.0 V		