



Pass and Seymour
PlugTail® Hospital Grade Extra Heavy Duty Surge Protective Duplex Receptacle, Blue
Part No. PT8300BLSP

PlugTail information, visit our PlugTail Headquarters.



Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.	Plated steel wrap strap design for maximum durability and corrosion resistance.
No exposed terminals create a finger safe application before, during, and after installation.	Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
Crimped and welded contacts.	Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
Large brass contacts snugly terminate on device blade terminals.	Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
Auto-ground clip assures positive ground.	For covering patents, see www.legrand.us/patents .

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Application Sector	Residential/Commercial	Standard	CSA Listed, cUL, UL Listed, RoHS, FSUL

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Phase	Single	Frequency Rating	60 Hz
Connection	Built-In Connector	Class	IG
Amperage	20 A	Type of Indicators	Audible Alarm, LED
Voltage	125.0 V	Environmental Conditions	UL94 V2