



PlugTail information, visit our PlugTail Headquarters.



Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Plated steel wrap strap design for maximum durability and corrosion resistance.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Large brass contacts snugly terminate on device blade terminals.

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Application Sector	Residential/Commercial	Standard	CSA Listed, cUL, UL Listed, RoHS, FSUL

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Phase	Single	Frequency Rating	60 Hz
Connection	Built-In Connector	Class	IG
Amperage	20 A	Type of Indicators	LED, Audible Alarm
Voltage	125.0 V	Environmental Conditions	UL94 V2
