



PT TESTER FOR RECEPT & TAILSFor detailed PlugTail information, visit our PlugTail Headquarters.

Features & Benefits

Ensures proper connections and power presence at both rough-in and device-out stages during P&S PlugTail Device Fast, easy identification of circuit connections. installation.

Easy-to-see indicator lights.

Sturdy construction for long-term dependability.

Helps prevent call backs.

Ensures proper wiring.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	China	Application Sector	Commercial

Dimensions

Product Width US	1.68 in	Product Depth US	1.06 in
Product Height US	3.93 in		

Technical Information

Amperage	15 A	Wire Size	12 AWG
----------	------	-----------	--------
