



Pass and Seymour
Discontinued - PlugTail® Hospital-Grade 15A USB Charging Receptacles, Gray
Part No. PTTR15HACUSBGRY



PlugTail® Hospital Grade USB Charging Receptacles provide the convenience of mobile charging without the need for a bulky AC adapter. This device is a perfect match for the constant needs of today's mobile environment and is rugged enough to withstand hard-use commercial applications. It comes equipped with two UL Fed Spec AC receptacles and two USB charging ports for mobile devices: one Type-A port and one Type-C port for newer products. An efficient, 15.5W power supply provides the power needed for charging mobile phones and tablets. The PlugTail® termination provides a more productive, secure, and safer installation and allows you to connect with the future of wiring device innovations. For detailed PlugTail® information, visit our PlugTail® Headquarters.

Features & Benefits

- AC receptacles are tamper resistant as standard : patented shutter system prevents improper insertion of foreign objects
 - Efficient, 15.5W power supply for fast charging of mobile phones and tablets
 - Triple-wipe, brass line contacts for 15A commercial applications
 - Multiple color options available
 - Zinc-plated steel for corrosion resistance
 - 5Vdc Type-C USB port to charge USB Type-C compatible mobile devices
 - PlugTail termination allows for more productive, finger-safe installation and added future flexibility
 - Stainless steel auto-ground clips assure positive ground
- Available in 15 & 20A, Specification Grade and Hospital Grade configurations

Specifications

General Info

| | | | |
|--------------|----------------|-------------------------|-----------------|
| Product Line | Pass & Seymour | Replaced by Part Number | PTTR15HACUSBGRY |
| Color | Gray | Country Of Origin | China |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 1.693 in | Product Depth US | 1.45 in |
| Product Height US | 2.677 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|------------------|-------|----------------|------|
| USB Amperage | 3.1 A | Number of USBs | 2 |
| USB Power Output | 15 W | Amperage | 15 A |
