



radiant Collection  
**radiant® Single-Pole 3-Way Vacancy Sensor, Black**  
Part No. RRW600VBK



Never worry about leaving the lights on, with the radiant® Vacancy Sensor. It automatically shuts off when a room is empty, and includes an adjustable delay setting of up to 20 minutes to match your needs. Designed for ease and style, it features a built-in locator light, and the sleek, clean lines of radiant® for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Passive infrared (PIR) sensor switch technology with 180° coverage up to 600 sq. ft. Rated for up to 600W (5A) of LED lighting.

Works with virtually any bulb/fixture, including: LED, incandescent, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp.

Turn the light on when you enter, and let it turn itself off automatically after you leave for true convenience. Perfect for bathrooms, hallways, closets, garages, and more.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

Features an adjustable time delay to off after no motion is detected. Delay settings range from 30 seconds to 20 minutes after the room is vacated (default 20 minute delay).

Manual ON/Auto OFF functionality. Meets California Title 24 requirements for automatic off lighting control.

Replace any basic light or fan switch in 15 minutes or less. Supports single pole and multi-location installs. No neutral required.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	China	Features	Motion Sensor
Switch Type	Motion Sensor	Application Sector	Residential

### Dimensions

Product Width US	1.69 in	Product Depth US	1.88 in
------------------	---------	------------------	---------

---

Product Height US	2.63 in
-------------------	---------

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Technical Information

---

Target Size	180 deg	Response Frequency	60 Hz
-------------	---------	--------------------	-------

---

Sensor Type	Vacancy	Amperage	5 A
-------------	---------	----------	-----

---

Number of Poles	Single Pole 3-Way	Indoor/Outdoor	Indoor
-----------------	-------------------	----------------	--------

---

Wattage	600 W	Mounting Type	Box
---------	-------	---------------	-----

---

Sensing Range	600 sq ft	Voltage	120 V
---------------	-----------	---------	-------

---

Sensitivity	60Hz	Load	120VAC
-------------	------	------	--------

---