



Pass and Seymour
Power Outlet Receptacle Openings, One Gang, Chrome
Part No. S384C



One Gang Power Outlet Receptacle Opening, 2.156 hole for 2.125 diameter device - 2 mtg. holes, Smooth Metal.

Features & Benefits

Chrome: .040" thick.

Lacquered to prevent corrosion.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Variety of special plated finishes.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications.

Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.

Packaged in protective film, with finish-matching screws.

Paintable to match plastic plates.

Specifications

General Info

| | | | |
|--------------------|------------------------|-------------------|---------------|
| Product Line | Pass & Seymour | Country Of Origin | United States |
| Application Sector | Residential/Commercial | | |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 2.75 in | Product Depth US | 0.2 in |
| Product Height US | 4.5 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|-----------------|--------------|-----------|---------|
| Cutout | Power Outlet | Thickness | 0.04 in |
| Number of Gangs | 1 | | |
