



Pass and Seymour  
Louver Plate, One Gang Horizontal, 302/304 Stainless Steel Painted Light Almond  
Part No. SS760LA



Smooth Metal Wall Plate 1-Gang Louver Horizontal 302/304 Stainless Steel Painted

Features & Benefits

|   |  |
|---|--|
| Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness.  | Brushed finish.  |
| This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.                                | Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist. |
| Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide. | Packaged in protective film, with finish-matching screws.  |
| Variety of special plated finishes.   | Paintable to match plastic plates.   |
| Can be silk-screened or engraved, and custom punched with over 300 opening styles.                                  |  |

Specifications

|                                       |                        |                   |               |
|---------------------------------------|------------------------|-------------------|---------------|
| General Info                          |                        |                   |               |
| Product Line                          | Pass & Seymour         | Country Of Origin | United States |
| Application Sector                    | Residential/Commercial | Standard          | CSA           |
| Dimensions                            |                        |                   |               |
| Product Width US                      | 2.75 in                | Product Depth US  | 0.2 in        |
| Product Height US                     | 4.5 in                 |                   |               |
| Listing Agencies / 3rd Party Agencies |                        |                   |               |
| cULus ListingNumber                   | 143223                 | cULus Listed      | Yes           |
| Technical Information                 |                        |                   |               |
| Cutout                                | Louver                 | Thickness         | 0.032 in      |

---

|                 |   |             |            |
|-----------------|---|-------------|------------|
| Number of Gangs | 1 | Orientation | Horizontal |
|-----------------|---|-------------|------------|

---