



Pass and Seymour  
Toggle Switch Openings, Three Gang, 302/304 Stainless Steel  
Part No. SSO3



Smooth Metal Wall Plate, Jumbo 3-Gang Toggle, 302/304  
Stainless Steel

Features & Benefits

- Type 302/304 Stainless Steel, non-magnetic: .032''' nominal thickness.
- Brushed finish.
- This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.
- Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Residential/Commercial	Standard	CSA

Dimensions

Product Width US	7.12 in	Product Depth US	0.2 in
Product Height US	5.25 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Cutout	Toggle	Thickness	0.032 in
--------	--------	-----------	----------

Number of Gangs	3
-----------------	---