



Smooth Metal Wall Plate, Jumbo 3-Gang Toggle, 302/304
Stainless Steel

Features & Benefits

Type 302/304 Stainless Steel, non-magnetic: .032"^{nominal thickness}.
Brushed finish.

This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.

Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Packaged in protective film, with finish-matching screws.

Variety of special plated finishes.

Paintable to match plastic plates.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Specifications

General Info

| | | | |
|--------------------|------------------------|-------------------|---------------|
| Product Line | Pass & Seymour | Country Of Origin | United States |
| Application Sector | Residential/Commercial | Standard | CSA |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 7.12 in | Product Depth US | 0.2 in |
| Product Height US | 5.25 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|--------|--------|-----------|----------|
| Cutout | Toggle | Thickness | 0.032 in |
|--------|--------|-----------|----------|

| | |
|-----------------|---|
| Number of Gangs | 3 |
|-----------------|---|
