



Pass and Seymour
Spec Grade Decorator Momentary Contact Switch, Ivory
Part No. TM811DTMOI



Specification Grade, Double-Throw, Momentary Contact Switch, 15A, 120V.

Features & Benefits

Impact-resistant face and body.

External screw-pressure-plate back and side wired.
Accepts #12 and #14 AWG.

Full wraparound metal strap with lock-in tabs.

Largest breadth of 15 amp offering.

Clear identification of circuits.

Ground screw position under the end of the strap minimizes the risk of contact.

Unique "Up/Down" switches match the look and feel of standard Decorator switches.

All screws are tri-drive.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	China	Application Sector	Residential/Commercial
Standard	UL 20	Type	Combination

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Amperage 15 A