



## Features & Benefits

2.1 A USB type A receptacle charges faster than other USB receptacles eliminates the need for bulky AC adapters.

Compact Design Tamper-Resistant receptacle and two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.

Back and side wire terminals accommodates #14 AWG - #10 AWG stranded and solid wire.

Tamper-Resistant, patented shutter system prevents improper insertion of foreign objects. Meets 2011 National Electrical Code: Tamper-Resistant requirements.

Stainless steel auto-ground clip assures positive ground. Zink-plated ground terminal screw

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Wire Size: #14 - #10 AWG Copper Conductor Only

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	TR5362USBW
Color	White	Country Of Origin	China
Application Sector	Commercial	Standard	CSA Listed, ETL Lsted, FSUL, UL Listed, RoHS

### Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

### Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
Phase	Single	Connection	Side & Back Wired
Number of Wires	3	Temperature Rating	-40° - 60° C

Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	125.0 V
Environmental Conditions	UL94 V2		