



Pass and Seymour

Discontinued - Hospital-Grade USB Charger with Tamper-Resistant 15A Duplex Receptacles, White

Part No. TR8200HUSBW



Features & Benefits

| | |
|---|---|
| Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices | AC receptacles available in 15 and 20 Amp, 125V |
| AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects. | Multiple color options available. |
| Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire. | Stainless steel auto-ground clips assure positive ground. |
| For covering patents, see www.legrand.us/patents . | |

Specifications

General Info

| | | | |
|--------------|----------------|-------------------------|--------------|
| Product Line | Pass & Seymour | Replaced by Part Number | TR15HUSBAC6W |
| Color | White | Country Of Origin | China |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|---------------------|-----|--------------|-------|
| Is Tamper-Resistant | Yes | USB Amperage | 3.1 A |
|---------------------|-----|--------------|-------|

| | | | |
|----------------|------|------------------|------|
| Number of USBs | 2 | USB Power Output | 15 W |
| Amperage | 15 A | | |