



Plate Kit For 2 Gang While-In-Use
Weatherproof Cover

Features & Benefits

Comply with NEC 2005 Section 406.8(B)(1) for wet locations covers, and conforms to NEMA 3R.

Covers mount vertically or horizontally.

Gasket made of closed cell foam, neoprene blend regular density, UL Rated HBF.

Single receptacle plate available in 1.405 inch and 1.595 inch openings.

Shallow covers accommodate up to 14/3 AWG extension cords.

Covers are self-closing as required by UL514C42.3.

Body, cover, and plates made of polycarbonate.

Mounting screws made of 302 stainless steel.

Deep model available for 20A locking plugs.

New trigger latch opens easily with one finger.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	United States	Application Sector	Residential/Commercial
Standard	UL Listed		

Listing Agencies / 3rd Party Agencies

cULus Listing Number	143222	cULus Listed	Yes
----------------------	--------	--------------	-----

Technical Information

Number of Outlets	1
-------------------	---