



Pass and Seymour
Trademaster® 15A/125V Duplex Receptacle, White
Part No. 3232W



Our Pass and Seymour TradeMaster® receptacles combine a traditional look with reliable, time-tested operation for any residential application.

Features & Benefits

Durable, high-quality construction

125-volt outlet

Wire Size: #12 - #14 AWG, Solid wire

Specifications

General Info

| | | | |
|-----------------------|------------------------|-------------------|---------------------------------|
| Product Line | Pass & Seymour | Color | White |
| Finish | Matte | Country Of Origin | China |
| Number of Receptacles | 2 | Outlet Type | Commercial, Indoor, Residential |
| Application Sector | Residential/Commercial | Standard | UL 498 |
| Type | Outlet | | |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 1.32 in | Product Depth US | 1.0 in |
| Product Height US | 3.31 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

Product Environmental Profile Yes

Technical Information

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 15 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|-----------|-------------|----------------|--------|
| Wire Size | 14 - 12 AWG | Indoor/Outdoor | Indoor |
|-----------|-------------|----------------|--------|

| | | | |
|---------|---------|--|--|
| Voltage | 125.0 V | | |
|---------|---------|--|--|
