



Cablofil
CabloPort Block 20" Long [943525]
 Part No. 943525



Cablo-Port is a UV and Weather resistant rubber base that creates a cushion between rooftop mounted equipment and sensitive roofing materials. Available in two styles, the Standard style is perfect for smaller loads and tight spaces and the Widebody design provides a broad base to minimize roof pressure and a larger area for glue application. Cablo-Port is also available with a wide variety of pre-mounted support options, including FAS P and Channel.

Features & Benefits

Cable pathway or other products mounted to base with clamps and screws.

Install: on any roofing material or other flat surface.

Curb style: maximum load 500 lbs. (CP5 - maximum load 150 lbs.).

Widebody design: has 1,000 lbs/ft maximum load and provides 5 times the surface to minimize roof material pressure, increase load capacity and provide over 120 square in/ft for glue application.

Composite material: allows through bolts or lag type screws (through bolts recommended)

Specifications

General Info

| | | | |
|--------------------|--------------|-------------------|-----------|
| Product Line | Cablofil | Finish | Other |
| UPC Number | 800388019102 | Country Of Origin | Canada |
| Application Sector | Commercial | Type | Fasteners |

Dimensions

| | | | |
|-------------------|-------------|-------------------|---------|
| Product Width US | 6.0 in | Product Weight US | 9.3 lb |
| Product Volume US | 0.271 cu ft | Product Depth US | 19.5 in |
| Product Height US | 4.0 in | | |

Buy American Act Compliance

| | |
|-----|-----|
| BAA | Yes |
|-----|-----|
