



Perfect for anywhere you'd like the combined power of on/off and dimmable lighting control. Turn lights on or off with a simple rocking motion, or slide to dim to your preferred light level. Use this dimmer switch on its own to control a 0-10V light or fixture from a single location, or pair with a 3-way switch to control a single light source from two locations.

This dimmer* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Usable in both single-pole and 3-way applications.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

For use with dimmable 0-10V bulbs or fixtures. Features smooth paddle action for turning lights on and off, plus easy slider for adjusting lights to your preferred light level.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Magnesium	Country Of Origin	China
Features	Antimicrobial Protection	Switch Type	Paddle
Number of Switches	1	Standard	cULus

Warranty Type	Limited Lifetime Warranty	Type	Dimmer
---------------	---------------------------	------	--------

Dimensions

Product Width US	1.77 in	Product Depth US	1.62 in
------------------	---------	------------------	---------

Product Height US	1.77 in
-------------------	---------

Technical Information

Electrical Rating	120V 10A (0-10V Fluorescent), 120V 10A (0-10V LED)	Connection	Screw Terminals
-------------------	--	------------	-----------------

Number of Gangs	1	Bulb Compatibility	Fluorescent, LED
-----------------	---	--------------------	------------------

Number of Poles	3-Way, Single Pole	Wattage	700 W
-----------------	--------------------	---------	-------

Mounting Type	Box	Voltage	0 to 10 V
---------------	-----	---------	-----------

Connection Type	Internal Pressure Plates	Load	LED, Fluorescent
-----------------	--------------------------	------	------------------
