

Commercial 1-Pole Switch, Side-Wire, 20A 120/277V.



## Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch life.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498/20		

### Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in
------------------	---------	------------------	----------

---

Product Height US	3.281 in
-------------------	----------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Technical Information

---

Actuator	Toggle	Contact Rating	120/277Vac, 20Amp
----------	--------	----------------	-------------------

---

Amperage	20 A	Action	Single Pole
----------	------	--------	-------------

---

Number of Poles	Single Pole	Voltage	120.0 V
-----------------	-------------	---------	---------

---