



Infinium 384 Offers ultra-high density Mini Duplex Connector (MDC) pass-through adapters which are organized to maximize fiber density while using the flexible and robust MDC connectors. These 1RU panels offer a density of 384 fibers (192 MDC Connectors) in a single unit of rack space. These panels have a front door to provide a clean look and to help protect the delicate cables. The rear support plate comes with two Multi-Use Mounting plates that feature eight HiLOC cradles. For cable management both the front and rear of the panel have several tiedown points to ensure proper routing, protection and a clean look for the fiber cables housed within the panel. The construction of the panel is powder-coated steel and is designed for optimal performance.

Features & Benefits

Panel Door: These panels have a front door to provide a clean look and to help protect the delicate cables

Cable Management Front: Four individual tie downs provide proper routing and protection of cables. While the front pillars ensure that cables do not pass the side egress point

Cable Management Rear: The rear support plate come with two Multi-Use Mounting plates that feature eight HiLOC cradles for quick and easy secure trunk mounting. While the rear support plate has 22 tie down points and 4 rear lip tie downs to maximize cable management and ensure proper routing

Splicing: The rear support plate also offers compatibility with the FST3-A144 splice tray, enabling ribbon splicing on this panel.

Includes Infinium 1U MDC Rack Mount Adapter Panel, Hook & Loop Straps, HiLoc Cradles, Mounting Hardware

Specifications

General Info

Product Line	Ortronics	Color	Magnesium
UPC Number	662875037415	Country Of Origin	Mexico
Type	Patch Panel		

Dimensions

Product Width US	19.0 in	Product Depth US	17.16 in
Product Height US	1.75 in		