



Wattstopper
DLM Wired Standard Shade Switch, 4B 1R, Ivory
Part No. BCS_WA_LMSH-SW241-I



LMSH-SW2xx Series Wall Switches are low voltage devices for manual control of shades from one or more locations. They are part of a Digital Lighting Management (DLM) system and can control any shade motors connected to DLM shade controllers

Features & Benefits

Switches are pre-engraved with most common control configurations

Low voltage pushbutton switches for control of multiple shades

Plug n' Go automatic configuration along with Pull n' Save and Push n' Learn for system personalization

Plug to other components using Cat 5e cables with RJ45connectors eliminating wiring errors

Matches 200-Series DLM lighting control switches for consistent design of lighting and shade control

Includes system configuration button for easy system programming from the switch

IR transceiver for wireless configuration and remote control

Components of Digital Lighting Management integrated shade control system

Custom engraving or engraved and non-engraved button kits available

Specifications

General Info

Product Line	Wattstopper	Color	Ivory
UPC Number	754182000593	Country Of Origin	United States
Package Quantity	1	Application Sector	Commercial
Warranty Type	5-Year	Type	Switch

Dimensions

Product Width US	1.6 in	Product Weight US	0.1 lb
Product Depth US	1.6 in	Product Height US	4.1 in

Additional Information

Product Has Potential to Contribute to LEED Yes

Technical Information

Compatibility	DLM	Number of Buttons	4
Indoor/Outdoor	Indoor	Wattage	0.12 W
Supply Voltage	24 V	Operating Temperature	0°-55°C
Environmental Conditions	5 to 95% (relative humidity, non-condensing)		
