



CABLOFIL WIRE MESH LOAD TABLE BASED ON MAXIMUM LOAD CAPACITY (NEMA)

CAT. NO.	DEPTH (in)	WIDTH (in)	LOAD IN LBS/FT PER SPAN			
			5	6	7	8
CF54/50	2	2	32.0	15.1	11.1	9.1
CF54/100	2	4	39.4	22.3	16.4	15.9
CF54/150	2	6	46.5	27.6	20.3	19.1
CF54/200	2	8	54.2	36.4	26.7	24.7
CF54/300	2	12	71.6	47.1	34.6	31.7
CF54/450	2	18	134.9	91.0	66.8	60.3
CF54/500	2	20	119.4	95.4	70.1	62.8
CF54/600	2	24	119.4	95.4	70.1	62.8
CF105/100	4	4	68.3	46.4	34.1	30.5
CF105/150	4	6	98.4	60.2	44.3	40.9
CF105/200	4	8	109.4	76.2	56.0	51.9
CF105/300	4	12	142.0	126.8	93.1	89.2
CF105/450	4	18	151.0	129.9	95.4	88.7
CF105/500	4	20	151.0	129.9	95.4	88.7
CF105/600	4	24	151.0	129.9	95.4	88.7
CF150/150	6	6	127.5	123.0	90.4	89.1
CF150/200	6	8	127.5	123.0	90.4	89.1
CF150/300	6	12	175.9	155.0	113.9	98.3
CF150/450	6	18	175.9	155.0	113.9	98.3
CF150/500	6	20	228.5	165.0	121.7	91.3
CF150/600	6	24	228.5	165.7	121.7	91.3
ZF150/900	6	36	228.5	165.7	121.7	91.3