

<u>Cat. No.*</u>	<u>Depth (Nominal) inches</u>	<u>Width (Nominal) inches</u>	<u>DESIGN LOAD (lb/ft at varying support spacings with S.F. of 1.5 (Span lengths))</u>					
			<u>SPAN LENGTH (feet)</u>					
			<u>5 ft</u>	<u>6 ft</u>	<u>7 ft</u>	<u>8 ft</u>	<u>9 ft</u>	<u>10 ft</u>
CF54/50	2	2	32.0	15.1	11.1	9.1	7.2	5.8
CF54/100	2	4	39.4	22.3	16.4	15.9	12.5	10.2
CF54/150	2	6	46.5	27.6	20.3	19.1	17.9	13.6
CF54/200	2	8	54.2	36.4	26.7	24.7	22.7	18.4
CF54/300	2	12	71.6	47.1	34.6	31.7	28.7	23.2
CF54/400	2	16	134.9	91.0	66.8	60.3	53.8	43.6
CF54/450	2	18	134.9	91.0	66.8	60.3	53.8	43.6
CF54/500	2	20	119.4	95.4	70.1	62.8	55.4	44.9
CF54/600	2	24	119.4	95.4	70.1	62.8	55.4	44.9
CF105/100	4	4	68.3	46.4	34.1	30.5	26.9	21.8
CF105/150	4	6	98.4	60.2	44.3	40.9	35	30.8
CF105/200	4	8	109.4	76.2	56.0	51.9	47.8	38.7
CF105/300	4	12	142.0	126.8	93.1	89.2	70.5	57.1
CF105/400	4	16	151.0	129.9	95.4	88.7	81.9	66.3
CF105/450	4	18	151.0	129.9	95.4	88.7	81.9	66.3
CF105/500	4	20	151.0	129.9	95.4	88.7	81.9	66.3
CF105/600	4	24	151.0	129.9	95.4	88.7	81.9	66.3
CF150/150	6	6	127.5	123.0	90.4	89.1	87.8	71.2
CF150/200	6	8	127.5	123.0	90.4	90	88	76
CF150/300	6	12	175.9	155.0	113.9	98.3	77.7	62.9
CF150/400	6	16	175.9	155.0	113.9	98.3	77.7	62.9
CF150/450	6	18	175.9	155.0	113.9	98.3	77.7	62.9
CF150/500	6	20	228.5	165.7	121.7	91.3	72.1	65.9
ZF150/600	6	24	228.5	165.7	121.7	91.3	72.1	58.4

* Includes prefix letters CF (waved) or ZF (straight) to indicate top wire style, waved or straight, respectively.