

## SEISMIC BRACING KITS 4-WAY



4-way cable kits are available in 5', 10', 15' and 20' lengths (an extra 4 feet of cable is added to any pre-cut length). Kits contain 4 lengths of cable and 4 oval sleeves. Stake eyes, bent on a 45 degree angle, are factory-installed on one end.

The gold 4-way cable kit includes 3/8" stake eyes. The orange and green 4-way cable kits include 1/2" stake eyes.

KITS	NUMBER	UL LOAD RATING	CABLE SIZE	CABLE COLOR	CABLE LENGTH	KIT INCLUDES
		LBS.	GAGE		FEET	
STANDARD GOLD KIT	PW12-4W38E-5	600	12	GOLD	5	(4) OVAL SLEEVES
STANDARD GOLD KIT	PW12-4W38E-10	600	12	GOLD	10	(4) OVAL SLEEVES
STANDARD GOLD KIT	PW12-4W38E-15	600	12	GOLD	15	(4) OVAL SLEEVES
STANDARD GOLD KIT	PW12-4W38E-20	600	12	GOLD	20	(4) OVAL SLEEVES
STANDARD ORANGE KIT	PW18-4W12E-5	1.100	18	ORANGE	5	(4) OVAL SLEEVES
STANDARD ORANGE KIT	PW18-4W12E-10	1.100	18	ORANGE	10	(4) OVAL SLEEVES
STANDARD ORANGE KIT	PW18-4W12E-15	1.100	18	ORANGE	15	(4) OVAL SLEEVES
STANDARD ORANGE KIT	PW18-4W12E-20	1.100	18	ORANGE	20	(4) OVAL SLEEVES
STANDARD GREEN KIT	PW36-4W12E-5	2.800	36	GREEN	5	(4) OVAL SLEEVES
STANDARD GREEN KIT	PW36-4W12E-10	2.800	36	GREEN	10	(4) OVAL SLEEVES
STANDARD GREEN KIT	PW36-4W12E-15	2.800	36	GREEN	15	(4) OVAL SLEEVES
STANDARD GREEN KIT	PW36-4W12E-20	2.800	36	GREEN	20	(4) OVAL SLEEVES