


D

ELECTRICAL PARAMETERS:

- DOUBLE-CONVERSION ONLINE, SINGLE-PHASE, 120V, 1.5kVA, 1.5kW
- INPUT TYPE: NEMA 5-15P, CORD
- OUTPUT TYPE: (8) NEMA 5-15R
- DISCHARGE TIME:
  - 100% LOAD 3.0 min.
  - 75% LOAD 5.3 min.
  - 50% LOAD 10.3 min.
  - 25% LOAD 26.2 min.


MECHANICAL PARAMETERS:

- WEIGHT 32.2 lbs.
- COLOR BLACK




LU-4PKIT-2U 4POST RAIL KIT, 2U

- (12) M6 RACK SCREWS
- (6) M6 CAGE NUTS



RACK MOUNT CONFIGURATION

INCLUDES L/R MOUNTING BRACKETS W/ SCREWS





TOWER CONFIGURATION

INCLUDES (4) FEET



C

C



B

B



DETAIL A  
NEMA 5-15P  
SCALE 1 : 2

ALSO INCLUDED:

- (1) USB CABLE 5'
- (1) MANUAL

A

A

*** NOTICE *** THIS DOCUMENT CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION INTENDED FOR USE ONLY BY THE INDIVIDUAL(S) PROVIDED. NEITHER THIS DOCUMENT, NOR ANY INFORMATION CONTAINED HEREIN, MAY BE COPIED, DISTRIBUTED, DISCLOSED TO ANY THIRD PARTY OR USED IN ANY MANNER OTHER THAN FOR WHICH IT HAS BEEN PROVIDED, WITHOUT THE PRIOR WRITTEN CONSENT OF LEGRAND						
DWN	NAME	DATE	SIZE	CAD FILE	DWG NO	REV
CHK	MM	3/6/2019	B	LU1500RTC	LU-1500-RT	00
APPR	RJG	3/7/2019	SCALE	1:4	SHEET	1 OF 1
	CV	3/18/2019				

WWW.LEGRAND.US

TITLE  
LEGRAND UPS ONLINE 1500VA, 120V, 50-60HZ

SIZE	CAD FILE	DWG NO	REV
B	LU1500RTC	LU-1500-RT	00
SCALE	1:4	SHEET	1 OF 1

4

3

2

1