



- NOTES
- OPTICAL PERFORMANCE CHARACTERISTICS SHALL BE IN ACCORDANCE WITH SPECIFICATION 71800079C.
 - EXTERNAL PORTS OF THE ADAPTERS HAVE PROTECTIVE DUST CAPS INSTALLED.
 - ASSEMBLY IDENTIFICATION LABEL SHALL CONTAIN ASSY PART NUMBER, DATE CODE (WWYY=WEEK YEAR), LOCATION CODE (XX), SERIAL NUMBER, "BB", "CC/125", & "12F" (USE TABLE 1 FOR "BB" & "CC").
 - THE "CCC" SUFFIX IN THE PART NUMBER DESIGNATES THE CORE SIZE OF FIBER.
 - LABEL SHOWING INSERTION LOSS VALUES, BY PORT, PROVIDED ASSEMBLED TO CASSETTE.
 - THE CASSETTE HOUSING IS BLACK ABS/PC. THE COVER IS CLEAR PC.
 - ALL DIMENSIONS ARE IN INCHES.
 - INTERNAL FIBER IS LOOSE FIBER.


⬡ DENOTES NOTE REFERENCE.



PORT LAYOUT (FRONT)



REAR LAYOUT (REAR)




FIBER COLOR BY PORT, POLARITY "ZZ" = A1	
HARNESS 1	
PORT #	COLOR
1	BLUE
2	ORANGE
3	GREEN
4	BROWN
5	SLATE
6	WHITE
7	RED
8	BLACK
9	YELLOW
10	VIOLET
11	ROSE
12	AQUA

FIBER TYPE				
"GGG"	TYPE	"X"	TIER	
09	SM 9/125 (OS2)	1	1	
09A	SM 9/125 (OS2)	1	1	
50E	MM 50/125 (4.9 GHz-km)	1	1	
		2	2	
		3	3	

"AA"	FRONT PNL ADAPTER
LA	LC (APC)
LC	LC (PC OR UPC)

TABLE 1 ⬡ ⬢ ⬣ ⬤

"GGG"	"BB"	"CC"	LC COLOR
09	SM	9	BLUE
09A	SM	9	GREEN
50E	MM	50	AQUA



PART NUMBER LEGEND

<p>*** NOTICE ***</p> <p>THIS DOCUMENT CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION INTENDED FOR USE ONLY BY THE INDIVIDUAL(S) PROVIDED. NEITHER THIS DOCUMENT, NOR ANY INFORMATION CONTAINED HEREIN, MAY BE COPIED, DISTRIBUTED, DISCLOSED TO ANY THIRD PARTY OR USED IN ANY MANNER OTHER THAN FOR WHICH IT HAS BEEN PROVIDED, WITHOUT THE PRIOR WRITTEN CONSENT OF LEGRAND, INC. MANUFACTURING RELEASE. PRODUCT SPECIFICATIONS AND STANDARDS ARE SUBJECT TO CHANGE WITHOUT NOTICE.</p>			WWW.LEGRAND.US		
<p>TITLE</p> <p>CASSETTE ASSY, M4, 12/F, LC DUPLEX, SPLICE</p>					
NAME	DATE	SIZE	CAD FILE	DWG NO	REV
DWN RJG	3/12/2018	B	M4AAD12GGGSSYZC	M4AAD12-GGGSSYZC	02
CHK DMS	3/12/2018	SCALE 1:2		SHEET 1 OF 1	
APPR RH	3/19/2018				