


RoHS

REV.	REVISION HISTORY	DATE
0	INITIAL RELEASE	21-JUN-2018



P/N CHART


50187_ 80987	18	5.49	5490	±100	±3.94
50188_ 80988	20	6.10	6100	±100	±3.94
P/N	FT	M	L	T(MM)	T(INCH)

③	HDMI CABLE, [(24AWG*1PAIR+DRAIN+AL+MY)*5PCS+24AWG*4 CONDUCTORS] +F+ADB,PVC JACKET,COLOR:BLACK	1
②	PVC MOLDING HOUSING,COLOR:BLACK	2
①	HDMI 19 PIN MALE CONNECTOR,METAL SHELL GOLD PLATED,INSULATOR COLOR:BLACK	2
ITEM	DESCRIPTIONS	Q'TY

DRAWING APPROVED			
PROPRIETARY & CONFIDENTIAL. THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF CABLES TO GO. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF CABLES TO GO IS PROHIBITED.			
	mm	TITLE HDMI 19M/HDMI 19M CABLE	
SCALE	NONE	CUS. NAME ORTRONICS	
SHEET	1/3	ENG. DATE Zhong 21-JUN-2018	
	DIMENSIONAL TOLERANCES UNLESS OTHERWISE NOTED	CHECKED DATE Susan 21-JUN-2018	
	REV. Ø	APPROVED DATE Macke 21-JUN-2018	
TITLE HDMI 19M/HDMI 19M CABLE		CUS. P/N SEE P/N CHART	
SCALE NONE		DWG. NO.	
SHEET 1/3		CUS. REV.	

REV.	REVISION HISTORY	DATE
0	INITIAL RELEASE	21-JUN-2018

SPECIFICATION (7/0.20Tx2C+D+AL+HM)*5C+7/0.20Tx4C+F+MY+AB24/10/0.10T OD:9.5			
I T E M		SPECIFICATION	
COMPONENT		COMPONENT A	COMPONENT B
Conductor	Constitution AWG/mm	7/0.20 (24AWG)	7/0.20 (24AWG)
	Material	TINNED COPPER STRANDED	TINNED COPPER STRANDED
	Cabling OD mm	0.6	0.6
Insulation	NO of wire	5P	4C
	Material	FOAM-PE+SKIN	HDPE
	OD mm	1.60±0.05	1.0±0.05
	Thickness mm	0.50 (REF)	0.20 (REF)
Shield	Drain	7/0.16T (26AWG)	/
	AL/Mylar	AL FACE INSIDE	/
	Hot-melt Mylar	Hot-melt Mylar	/
	Filler	FILLER	
	Mylar	MYLAR	
Shield	AL/Mylar	AL FACE OUTSIDE.	
	Constitution N/mm	24/10/0.10	
	Material	TINNED COPPER WIRE	
	Coverage %	85%	
Jacket	OD mm	9.5±0.25	
	Material	PVC (CL3 FT4)	
	Thickness mm	0.85 (REF)	
	Hardness A	SHORE.A 80±3	
UL (Style)		UL	
MARKING :		Premium High Speed HDMI™ Cable with Ethernet E468040 (UL) CL3 75℃ 24AWG E468039 (UL) CMG c(UL) 75℃ FT4 24AWG	




P/N CHART

50187_80987	18	5.49	5490	±100	±3.94
50188_80988	20	6.10	6100	±100	±3.94
P/N	FT	M	L	T(MM)	T(INCH)

DRAWING APPROVED			
PROPRIETARY & CONFIDENTIAL. THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF CABLES TO GO. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF CABLES TO GO IS PROHIBITED.			
	mm	TITLE	
SCALE	NONE	HDMI 19M/HDMI 19M CABLE	
SHEET	2/3	CUS. NAME	
	DIMENSIONAL TOLERANCES UNLESS OTHERWISE NOTED X ± =0.5 (0.020") XXX ± =0.050 (0.001") REV. ø	CUS. P/N	ENG. DATE Zhang 20-JUN-2018
		SEE P/N CHART	CHECKED DATE Susan 20-JUN-2018
	CUS. REV.	DWG. NO.	APPROVED DATE Macke 20-JUN-2018


REV.	REVISION HISTORY	DATE
0	INITIAL RELEASE	21-JUN-2018




CARTON MARKINGS

SIDE MARKING	FRONT MARKING
P/N: Q'TY: N. T.: G. T.: MEA'T	PCS KGS KGS (PLACE OF DELIVERY) P/O C/NO (MADE IN CHINA)

BAR CODE LABEL



DATE CODE LABEL



MATTERS NEED ATTENTION:

- 1.Put a waterproof bag in the carton, Every carton pcs.
- 2.Top and bottom put a cardboard, sealed by clear tape.

BAR CODE LABEL

"XXXXX"= 5 DIGIT PART NUMBER

"XX"= LENGTH. SEE P/N CHART

50187_80987	5490±100	240±10	30	22PCS
50188_80988	6100±100	240±10	35	20PCS
P/N	L	Diameter	Height	Qty/water proof PE bag

DRAWING APPROVED

PROPRIETARY & CONFIDENTIAL. THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF CABLES TO GO. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF CABLES TO GO IS PROHIBITED.

SCALE	mm	TITLE	HDMI 19M/HDMI 19M CABLE
SHEET	NDINE	CUS. NAME	ORTRONICS
	3/3	CUS. P/N	SEE P/N CHART
		DWG. NO.	

ENG. DATE

Zhang 20-JUN-2018

CHECKED DATE

Susan 20-JUN-2018

APPROVED DATE

Macke 20-JUN-2018

GET CONNECTED